

Schematic Drawings of Mega-Strip (Strip array) (unit=mm) 2003-July-31 Y.Fujii (KEK)

## Glued Mega-strip

- 20 individual strips are glued together with white glue.
- Strip pitch must be precise (10.0±0.1mm).
- Strip width be sligtly narrower than 10.0mm to make narrow gap for glue.
- Gap be narrower than 0.5mm.

## Gap (width=d) filled with white glue 10.0±0.1 10.0±0.1 10.0±0.1 200mm±0.5mm (20 strips)

## Machined Mega-strip

- Large plate (200mm x 200mm) are machined to be 20 individual strips by making isolation grooves.
- Strip pitch must be precise (10.0±0.05mm).
- Strip width be sligtly narrower than 10.0mm to make isolation groove.
- Isolation groove be narrower than 0.5mm.
- Isolation groove be deeper than 1.7mm.
- Isolation groove be filled with white paint.

